

ProofTainer Max +18G/+23G

[va-Q-tainer MAXx +18G/+23G]

For +15 °C to +25 °C shipments

Envirotainer^o

Precision with Purpose



Product picture shows an exemplary solution without temperature batteries

DESCRIPTION

Delivering superior performance while streamlining handling, the ProofTainer family features six sizes, accommodating from 0.5 – 2 EU or 1 - 2 US pallets. Whether you're shipping clinical trials or commercial drugs, we ensure consistent temperature control throughout your products journey. With qualified temperature ranges from -70°C to +20°C and over 120 hours of autonomy, ProofTainer provides optimal conditions for your sensitive cargo, delivering the flexibility you need for your product requirements.

DIMENSIONS AND WEIGHT

External Dimensions (l x w x h)		Internal Dimensions ¹ (d x h)		Tolerances	
[mm]	[inch]	[mm]	[inch]	[mm]	[inch]
1796 x 1680 x 2110	70.7 x 66.1 x 83.1	1100 x 1720	43.3 x 67.7	± 8	± 0.3

Tare Weight ¹		Volumetric weight		Maximum Payload (Weight)		Payload ¹ (Volume)
[kg]	[lbs]	[kg]	[lbs]	[kg]	[lbs]	[L]
1344 ± 20	2963 ± 44.1	1061	2339.1	1450	3196.7	1664

¹Including Temperature Batteries

TEMPERATURE BATTERY CONFIGURATION

ProofBlok	Pieces	Dimensions ² (l x w x h)		Weight		Material number
		[mm]	[inch]	[kg]	[lbs]	
27L +18G	60	470 x 275 x 32	18.5 x 10.8 x 1.3	3.1	6.8	AK000110
27L +23G	30	470 x 275 x 32	18.5 x 10.8 x 1.3	3.1	6.8	AK000111

²dimensions of empty Temperature Battery shell, variation due to PCM inside and aggregation state possible

PERFORMANCE The ProofTainer Max +18G/+23G is qualified in the temperature range from +15 °C to +25 °C

Temperature scenario	Duration [hrs]	Kelvin-hours ³	Average ambient temperature [°C]
ISTA 7D summer	≥ 133	≥ 1303	+29.8
ISTA 7D winter	> 144	< -2160	+5

³Detailed information about the concept of Kelvin-hours on www.kelvinhours.com

For more details, please view the qualification report. Before performing a shipment with the ProofTainer Max +18G/+23G it is suggested that the user performs a validation process with the equipment available and under the conditions available. A test in worst case conditions is recommended. The box provides a very stable and well-designed system solution which has to be adapted on the particular requirements of the user.

For more information please contact support@envirotainer.com.