OnePak 4 +05G EL (Article number: BC000723)

[va-Q-one 4 +05G EL]

For +2 °C to +8 °C shipments





Product picture shows an exemplary solution for the temperature range +2 °C to +8 °C

DESCRIPTION

Specifically designed for door-to-door pharmaceutical distribution of smaller volumes to remote locations, OnePak ensures your products reach even the most inaccessible areas without compromising quality or efficacy. This single-use solution is ideal for regions with limited logistics services, eliminating the need for return shipping and ensuring consistent access to medicines.

Date: 2024-08-21 Page: 1 of 2 Version: 14391

OnePak 4 +05G EL (Article number: BC000723)

[va-Q-one 4 +05G EL]

For +2 °C to +8 °C shipments



DIMENSIONS AND WEIGHT

| External Dimensions (1 x w x h) | | Internal Dimensi | ons ¹ (1 x w x h) | Tolerances | |
|---------------------------------|--------------------|------------------|------------------------------|------------|--------|
| [mm] | [inch] | [mm] | [inch] | [mm] | [inch] |
| 360 x 345 x 370 | 14.2 x 13.6 x 14.6 | 165 x 165 x 165 | 6.5 x 6.5 x 6.5 | ± 5 | ± 0.2 |

| Tare W | eight ¹ | Payload ¹ (Volume) | |
|--------|--------------------|-------------------------------|--|
| [kg] | [lbs] | [L] | |
| 9 ± 1 | 19.8 ± 2.2 | 4 | |

¹including Temperature Batteries

TEMPERATURE BATTERY CONFIGURATION

| OneBlok Pieces | Pieces | Dimensions ² (1 x w x h) | | Weight | | Material number |
|----------------|--------|-------------------------------------|-----------------|--------|-------|-----------------|
| | | [mm] | [inch] | [kg] | [lbs] | |
| 20204 +05G EL | 6 | 200 x 200 x 39 | 7.9 x 7.9 x 1.5 | 1.1 | 2.4 | AK000448 |

²dimensions of empty Temperature Battery shell, variation due to PCM inside and aggregation state possible

PERFORMANCE The OnePak 4 +05G EL is qualified in the temperature range from +2 °C to +8 °C

| Temperature scenario | Duration [hrs] | Kelvin-hours ³ | Average ambient temperature [°C] |
|----------------------|-------------------|---------------------------|-------------------------------------|
| ISTA 7D summer | ≥ 127 | ≥ 3175 | +30 |
| ISTA 7D winter | > 144 | n.a. | +5 |

³Detailed information about the concept of Kelvin-hours on www.kelvinhours.com

For more details, please view the qualification report. Before performing a shipment with the OnePak 4 +05G EL it is suggested that the user performs a validation process with the equipment available and under the conditions available. A test in worst case conditions is recommended. The box provides a very stable and well-designed system solution which has to be adapted on the particular requirements of the user.

For more information please contact support@envirotainer.com.