ProofTainer US -37G

[va-Q-tainer USx -37G]

For -40 °C shipments





Product picture shows an exemplary solution for the temperature range +2 °C to +8 °C

DESCRIPTION

Delivering superior performance while streamlining handling, the ProofTainer family features six sizes, accommodating from 0.5 – 2 EU or 1 - 2 US pallets. Whether you're shipping clinical trials or commercial drugs, we ensure consistent temperature control throughout your products journey. With qualified temperature ranges from -70°C to +20°C and over 120 hours of autonomy, ProofTainer provides optimal conditions for your sensitive cargo, delivering the flexibility you need for your product requirements.

ProofTainer US -37G

[va-Q-tainer USx -37G]

For -40 °C shipments



DIMENSIONS AND WEIGHT

External Dimensions (1 x w x h)		Internal Dimensi	ons ¹ (1 x w x h)	Tolerances	
[mm] [inch]		[mm] [inch]		[mm]	[inch]
1423 x 1490 x 1580	56 x 58.7 x 62.2	1200 x 1250 x 1220	47.2 x 49.2 x 48	± 8	± 0.3

Tare Weight ¹		Volumetric weight		Maximum Payload (Weight)		Payload ¹ (Volume)
[kg]	[lbs]	[kg]	[lbs]	[kg]	[lbs]	[L]
684 ± 20	1508 ± 44.1	558	1230.2	1200	2645.5	1755

¹including Temperature Batteries

TEMPERATURE BATTERY CONFIGURATION

ProofBlok	Pieces	Dimensions ² (1 x w x h) [mm] [inch]		Weight [kg] [lbs]		Material number
27L -37G	52	470 x 275 x 32	18.5 x 10.8 x 1.3	5.3	11.7	AK000296

²dimensions of empty Temperature Battery shell, variation due to PCM inside and aggregation state possible

PERFORMANCE The ProofTainer US -37G is qualified in the temperature range below -20 °C

Temperature scenario	Duration [hrs]	Kelvin-hours ³	Average ambient temperature [°C]
controlled summer	≥ 99	≥ 4950	+20
extreme summer	63	n.a.	+49.2

 $^{^{\}rm 3}{\rm Detailed}$ information about the concept of Kelvin-hours on www.kelvinhours.com

For more details, please view the qualification report. Before performing a shipment with the ProofTainer US -37G it is suggested that the user performs a validation process with the equipment available and under the conditions available. A test in worst case conditions is recommended. The box provides a very stable and well-designed system solution which has to be adapted on the particular requirements of the user.

For more information please contact support@envirotainer.com.